



P64AX1.0PVC3

**P64AX c/w 4 Core 1.00mm<sup>2</sup> 3m PVC Lead**

**Technical Features**

**Architecture**

Number of poles	4
-----------------	---

**Voltage**

Max. operating voltage	240 V
------------------------	-------

**Electric current**

Rated current	6 A
---------------	-----

**Cable**

Cable length	3 m
--------------	-----

**Dimensions**

Length	1000 mm
--------	---------

**Connection**

Conductor cross-section	1 - 1 mm <sup>2</sup>
-------------------------	-----------------------

**Equipment**

Mechanical coding	Yes
-------------------	-----

Type cable side 1	Plug
-------------------	------

Type cable side 2	Free conductor end
-------------------	--------------------

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

**Materials**

Colour	White
--------	-------

**Cable**

Cable permanent temperature resistant to	90 °C
--	-------

**Sustainability**

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----