



P64AXI1.0PVC!3

P64AX c/w 4 Core 1.00mm² 3m PVC Lead

Technical Features

Architecture

| | |
|-----------------|---|
| Number of poles | 4 |
|-----------------|---|

Voltage

| | |
|------------------------|-------|
| Max. operating voltage | 240 V |
|------------------------|-------|

Electric current

| | |
|---------------|-----|
| Rated current | 6 A |
|---------------|-----|

Cable

| | |
|--------------|-----|
| Cable length | 3 m |
|--------------|-----|

Dimensions

| | |
|--------|---------|
| Length | 1000 mm |
|--------|---------|

Connection

| | |
|-------------------------|-----------------------|
| Conductor cross-section | 1 - 1 mm ² |
|-------------------------|-----------------------|

Equipment

| | |
|-------------------|-----|
| Mechanical coding | Yes |
|-------------------|-----|

| | |
|-------------------|------|
| Type cable side 1 | Plug |
|-------------------|------|

| | |
|-------------------|--------------------|
| Type cable side 2 | Free conductor end |
|-------------------|--------------------|

Use conditions

| | |
|----------------------------------------------------------|---|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
|----------------------------------------------------------|---|

Materials

| | |
|--------|-------|
| Colour | White |
|--------|-------|

Cable

| | |
|------------------------------------------|-------|
| Cable permanent temperature resistant to | 90 °C |
|------------------------------------------|-------|

Sustainability

| | |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|