



P64AX1.0PVC15

P64AX c/w 4 Core 1.00mm² 5m PVC Lead

Technical Features

Architecture

Number of poles 4

Voltage

Max. operating voltage 240 V

Electric current

Rated current 6 A

Cable

Cable length 5 m

Dimensions

Length 1000 mm

Connection

Conductor cross-section 1 - 1 mm²

Equipment

Mechanical coding Yes

Type cable side 1 Plug

Type cable side 2 Free conductor end

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2 2

Materials

Colour White

Cable

Cable permanent temperature resistant to 90 °C

Sustainability

REACH-SVHC free Yes

RoHS conform Yes