



KDN280A

Insulated busbar 2P 80A fork 16mm² 12M

Technical Features

Electric current

| | |
|---------------|------|
| Rated current | 80 A |
|---------------|------|

Architecture

| | |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

Dimensions

| | |
|--------|--------|
| Length | 210 mm |
|--------|--------|

Voltage

| | |
|--------------------------------------|--------|
| Rated impulse withstand voltage Uimp | 4500 V |
|--------------------------------------|--------|

| | |
|------------------------------|-------------|
| Rated operational voltage Ue | 230 - 400 V |
|------------------------------|-------------|

Connection

| | |
|-------------------------------|--------------------|
| Cross-section rigid conductor | 16 mm ² |
|-------------------------------|--------------------|

| | |
|---------------------|------------------------|
| Connector/plug type | Phase busbar with fork |
|---------------------|------------------------|

Capacity

| | |
|-------------------|----|
| Number of modules | 12 |
|-------------------|----|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|