




EHN711



Daily time switch 1 channel, analog, 72x72 with power reserve

Technical Features

Equipment

Number of channels	1
--------------------	---

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Power consumption during operation	0.7 W
230 V incandescent and halogen lamp	1600 W
Power incandescent lamp	1000 - 1000 W

Functions

Number of function channels	1
-----------------------------	---

Connection

Number of contacts	1
Cross-section flexible conductor	1 - 2.5 mm ²
Cross-section rigid conductor	1 - 2.5 mm ²

Use conditions

Operating temperature	-10 - +45 °C
-----------------------	--------------

Capacity

Number of modules	4
-------------------	---

Dimensions

Height	72 mm
Width	72 mm
Depth	50 mm

Texts

Switch mode	Change-over contact
Installation mode	For surface mounting

Endurance

Electrical durability at nominal load in AC1 in operating cycles	50000
--	-------

Texts

Type of connection	With screw terminals
--------------------	----------------------

Voltage

Rated operational voltage U _e	230 - 240 V
--	-------------

Settings

Programme cycles	Programme cycle: 24 hours
Shortest switching time	15 min

Lighting

LED lamp power	70 W
----------------	------

Sustainability

Halogen free	Yes
RoHS conform	Yes