



LF325M

Cylindrical fuse-links for industrial applications 10x38mm aM 25A 400V AC 120kA

**Technical Features**

**Fuse**

Fuse characteristics	aM
Fuse size	10.3 x 38

**Electric current**

Rated current	25 A
---------------	------

**Power**

Total power loss under IN	1.40 W
---------------------------	--------

**Main electrical attributes**

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	120 kA
---	--------

**Voltage**

Type voltage supply	AC
Nominal voltage	400 - 400 V

**Architecture**

Curve	C
-------	---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes