



SPB065R

Cartridge L-N Uc 320V In 20kA Imax 65kA Up 1,35kV

Technical Features

Capacity

Number of modules	1
-------------------	---

Voltage

Rated operational voltage Ue	240 - 415 V
Continuous operating voltage Uc according to IEC 61643-1	305 V
Voltage protection level Up according to IEC 61643-1	1.45 kV
Type voltage supply	AC

Electric current

Nominal discharge current In 8 - 20 μ s L-N(PEN)/N-PE IEC 61643	20 kA
---	-------

Dimensions

Height	52.4 mm
Width	17.5 mm
Depth	55.3 mm

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Network configuration

Network type	TN-C TN-S TT
--------------	--------------------

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	3 - 3 Nm
---------------------------	----------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes