



LF540M

Cylindrical fuse-links for industrial applications 22x58mm aM 40A 690V AC 120kA

**Technical Features**

**Fuse**

Fuse characteristics	aM
Fuse size	22 x 58

**Electric current**

Rated current	40 A
---------------	------

**Power**

Total power loss under IN	3.40 W
---------------------------	--------

**Main electrical attributes**

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	80 kA
---	-------

**Voltage**

Type voltage supply	AC
Nominal voltage	690 - 690 V

**Architecture**

Curve	C
-------	---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes