



LF590G

Cylindrical fuse-links for industrial applications 22x58mm gG 100A 500V AC 120kA

**Technical Features**

**Fuse**

Fuse characteristics	gG
Fuse size	22 x 58

**Electric current**

Rated current	100 A
---------------	-------

**Power**

Total power loss under I <sub>N</sub>	9 W
---------------------------------------	-----

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	120 kA
---	--------

**Voltage**

Type voltage supply	AC
Nominal voltage	500 - 500 V

**Architecture**

Curve	C
-------	---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes