



LF408G

**Industrial fuse-links 14x51 gG 8A**

**Technical Features**

**Fuse**

Fuse characteristics	gG
Fuse size	14 x 51

**Electric current**

Rated current	8 A
Rated breaking capacity I <sub>t</sub> at 500 V AC IEC 60269-2	120 kA

**Power**

Total power loss under I <sub>N</sub>	1 W
---------------------------------------	-----

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	80 kA
---	-------

**Voltage**

Type voltage supply	AC
Nominal voltage	690 - 690 V

**Architecture**

Curve	C
-------	---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes