



SPB408D

Surge Protection Device 4P TNS/TT Uc 275V In 2 kA I_{max} 8 kA U_p 1kV

Technical Features

Capacity

Number of modules	4
-------------------	---

Voltage

Rated operational voltage U _e	240 - 415 V
Continuous operating voltage U _c according to IEC 61643-1	275 V
Voltage protection level U _p according to IEC 61643-1	0.90 kV
Voltage protection level U _p L-PE/N-PE according to IEC 61643-11	1.50 kV
Voltage level U _p L-N/PEN IEC 61643-11	900 V

Electric current

Nominal discharge current I _n 8 - 20 μs L-N(PEN)/N-PE IEC 61643	2 kA
	20 kA
Max. overcurrent protection device, parallel connection (fuse)	125 A
Max. discharge (I _{max}) L-N(PEN)/ N-PE	8 kA
	40 kA

Dimensions

Height	89.80 mm
Width	71 mm
Depth	65.7 mm

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Network configuration

Network type	TN-S
	TT

Equipment

With remote signalling contact	No
--------------------------------	----

Connection

Cross-section of input and output with screws, for flexible conductors	1.5 - 25.0 mm ²
Cross-section of input and output with screws, for massive conductors	1.5 - 35.0 mm ²

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	3 - 4.5 Nm
---------------------------	------------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes