



EE638

LED floodlight 3000 Lumen, white

Technical Features

Detection

With light sensor	No
-------------------	----

Controls and indicators

Applicable with movement sensor	No
---------------------------------	----

Installation, mounting

Ceiling mounting possible	No
---------------------------	----

Lighting

Colour temperature	4000 - 4000 K
--------------------	---------------

Safety

Impact resistance IK	IK04
----------------------	------

Equipment

Adjustable	Yes
------------	-----

Scope of delivery

Lamp included	Yes
---------------	-----

Dimensions

Length	226 mm
--------	--------

Width	136 mm
-------	--------

Height	141 mm
--------	--------

Lighting

Lumen	3000 lm
-------	---------

Materials

Material	Plastic
----------	---------

Lighting

Number of lamps	30
-----------------	----

Materials

RAL code	9010
----------	------

Power

Rated power system	30 W
--------------------	------

Connection

Suitable for through wiring	Yes
-----------------------------	-----

Installation, mounting

Suitable for wall mounting	Yes
----------------------------	-----

Voltage

Type voltage supply	AC
---------------------	----

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----