Product Datasheet
EE634



EE634

LED floodlight 3000 Lumen with movement detector, white

Technical Features

Detection	
With light sensor	Yes
Controls and indicators	
Applicable with movement sensor	Yes
Installation, mounting	
Ceiling mounting possible	No
Lighting	
Colour temperature	4000 - 4000 K
Safety	
Impact resistance IK	IK04
Ingress Protection (IP) class	IP55
Equipment	
Adjustable	Yes
Scope of delivery	
Lamp included	Yes
Dimensions	
Length	226 mm
Width	156 mm
Height	141 mm
Lighting	
Lumen	3000 lm
Materials	
Material	Plastic
Lighting	
Number of lamps	30
Materials	
RAL code	9010
Power	
Rated power system	30 W
Connection	
Suitable for through wiring	Yes
Installation, mounting	
Suitable for wall mounting	Yes
Voltage	
Type voltage supply	AC
Sustainability	
REACh-SVHC free	Yes
RoHS conform	Yes