



SPN715D

**SPD 2P auto-protected pluggable 15kA class 2 with end of life indicator**

**Technical Features**

**Capacity**

Number of modules	2
-------------------	---

**Voltage**

Rated operational voltage $U_e$	230 - 230 V
Continuous operating voltage $U_c$ according to IEC 61643-1	275 V
Voltage protection level $U_p$ according to IEC 61643-1	1.50 kV

**Electric current**

Nominal discharge current $I_n$ 8 - 20 $\mu$ s L-N(PEN)/N-PE IEC 61643	5 kA 20 kA
Max. discharge ( $I_{max}$ ) L-N(PEN)/ N-PE	15 kA

**Dimensions**

Height	82 mm
Width	44 mm
Depth	103 mm

**Use conditions**

Operating temperature	-40 - 55 °C
-----------------------	-------------

**Network configuration**

Network type	TN TT
--------------	----------

**Equipment**

With remote signalling contact	No
--------------------------------	----

**Standards**

Requirement class IEC 61643	T2
-----------------------------	----

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Installation, mounting**

Nominal tightening torque	3.60 - 3.60 Nm
---------------------------	----------------