



EVN011



**Remote Control Dimmer universal 300W**

**Technical Features**

**Voltage**

Operating voltage	230 - 230 V
Rated operational voltage U <sub>e</sub>	230 - 230 V

**Connectivity**

With bus system KNX radio	No
---------------------------	----

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Grey
RAL code	7035
Material	Plastic

**Dimensions**

Height	90 mm
Width	17.50 mm
Depth	65 mm

**Architecture**

Control/operation element	Single push button
---------------------------	--------------------

**Power**

Power consumption during operation	2.10 VA
Power consumption standby	0.2 W
230 V incandescent and halogen lamp	300 W
Power incandescent lamp	300 - 300 W

**Lighting**

Dimmable 230 V LED lamp	60 - 60 W
LED lamp power	60 W

**Use conditions**

Operating temperature	-10 - +45 °C
-----------------------	--------------

**Connection**

Cross-section rigid conductor	1.5 - 6 mm <sup>2</sup>
Cross-section flexible conductor	1.5 - 6 mm <sup>2</sup>

**Capacity**

Number of modules	1
-------------------	---

**Texts**

Dimming principle	Automatic load detection
Fuse	With electronic short-circuit and overload protection
Installation mode	For mounting on DIN rail
Type of connection	With screw terminals

**Sustainability**

RoHS conform	Yes
--------------	-----