



EVN011



### Remote Control Dimmer universal 300W

#### Technical Features

##### Voltage

Operating voltage	230 - 230 V
Rated operational voltage U <sub>e</sub>	230 - 230 V

##### Connectivity

With bus system KNX radio	No
---------------------------	----

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Colour	Grey
RAL code	7035
Material	Plastic

##### Dimensions

Height	90 mm
Width	17.50 mm
Depth	65 mm

##### Architecture

Control/operation element	Single push button
---------------------------	--------------------

##### Power

Power consumption during operation	2.10 VA
Power consumption standby	0.2 W
230 V incandescent and halogen lamp	300 W
Power incandescent lamp	300 - 300 W

##### Lighting

Dimmable 230 V LED lamp	60 - 60 W
LED lamp power	60 W

##### Use conditions

Operating temperature	-10 - +45 °C
-----------------------	--------------

##### Connection

Cross-section rigid conductor	1.5 - 6 mm <sup>2</sup>
Cross-section flexible conductor	1.5 - 6 mm <sup>2</sup>

##### Capacity

Number of modules	1
-------------------	---

##### Texts

Dimming principle	Automatic load detection
Fuse	With electronic short-circuit and overload protection
Installation mode	For mounting on DIN rail
Type of connection	With screw terminals

##### Sustainability

RoHS conform	Yes
--------------	-----