




80262260



**R.x KNX (TP+EASY) Movement detector module 2,20m**

**Technical Features**

**Dimensions**

Recommended installation height 2.20 - 2.20 m

**Settings**

Supported configuration mode ETS  
easy  
Minimal duty cycle 10 s

**Functions**

Maximal duty cycle 30 min

**Connectivity**

With bus system KNX radio No

**Voltage**

Operating voltage over bus 21 - 32 V

**Scope of delivery**

Bus connection included Yes

**Electric current**

Bus current consumption data transfer 10 mA

**Lighting**

Response brightness adjustable 5 - 1000 lx

**Detection**

Detection angle adjustable 45 - 90 °

Detection angle horizontal 90 - 180

**Use conditions**

Operating temperature -5 - 45 °C

**Materials**

Material Metal  
Plastic

**Texts**

Push button With button for automatic/permanent ON/permanent OFF  
Operating mode With 3 operating modes: automatic/permanent ON/permanent OFF  
Function Presence simulation  
With party function  
Installation mode With spreader claws  
With dismantling protection

**Sustainability**

RoHS conform Yes