



TXB344



**Binary input 4 fold + LED output 4 fold, flush mounted, KNX**

**Technical Features**

**Architecture**

Bus system EIB

**Settings**

Supported configuration mode ETS  
easy

**Electric current**

Number of entry circuits 4

**Equipment**

External signal voltage necessary Yes

**Connectivity**

With bus system KNX radio No

**Equipment**

Radio frequency bidirectional No

With battery No

With HVAC control No

**Installation, mounting**

Mounting on Flush mounting

**Lighting**

LED controlling Yes

**Materials**

Material Polyamide (PA)

Colour Light grey

RAL code 7035

**Safety**

Ingress Protection (IP) class IP20

**Use conditions**

Operating temperature 0 - 45 °C

**Voltage**

Input voltage 5 - 5 V

Operating voltage over bus 21 - 32 V

Type voltage supply DC

System supply voltage 30 V DC Via bus

**Texts**

Installation mode For flush-mounted and hollow wall mounting

Type of connection With pre-assembled cable

**Sustainability**

RoHS conform Yes