



TXB344



**Binary input 4 fold + LED output 4 fold, flush mounted, KNX**

**Technical Features**

**Architecture**

Bus system	EIB
------------	-----

**Settings**

Supported configuration mode	ETS easy
------------------------------	-------------

**Electric current**

Number of entry circuits	4
--------------------------	---

**Equipment**

External signal voltage necessary	Yes
-----------------------------------	-----

**Connectivity**

With bus system KNX radio	No
---------------------------	----

**Equipment**

Radio frequency bidirectional	No
With battery	No
With HVAC control	No

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Lighting**

LED controlling	Yes
-----------------	-----

**Materials**

Material	Polyamide (PA)
Colour	Light grey
RAL code	7035

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	0 - 45 °C
-----------------------	-----------

**Voltage**

Input voltage	5 - 5 V
Operating voltage over bus	21 - 32 V
Type voltage supply	DC
System supply voltage	30 V DC Via bus

**Texts**

Installation mode	For flush-mounted and hollow wall mounting
Type of connection	With pre-assembled cable

**Sustainability**

RoHS conform	Yes
--------------	-----