



TXA306



**Binary input 6 fold, universal, modular, KNX**

**Technical Features**

**Architecture**

|            |     |
|------------|-----|
| Bus system | EIB |
|------------|-----|

**Settings**

|                              |             |
|------------------------------|-------------|
| Supported configuration mode | ETS<br>easy |
|------------------------------|-------------|

**Electric current**

|                          |   |
|--------------------------|---|
| Number of entry circuits | 6 |
|--------------------------|---|

**Equipment**

|                                   |    |
|-----------------------------------|----|
| External signal voltage necessary | No |
|-----------------------------------|----|

**Connectivity**

|                           |    |
|---------------------------|----|
| With bus system KNX radio | No |
|---------------------------|----|

**Equipment**

|                               |    |
|-------------------------------|----|
| Radio frequency bidirectional | No |
| With battery                  | No |
| With HVAC control             | No |

**Installation, mounting**

|             |          |
|-------------|----------|
| Mounting on | DIN rail |
|-------------|----------|

**Lighting**

|                 |    |
|-----------------|----|
| LED controlling | No |
|-----------------|----|

**Materials**

|          |            |
|----------|------------|
| Material | Plastic    |
| Colour   | Light grey |
| RAL code | 7035       |

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Use conditions**

|                       |           |
|-----------------------|-----------|
| Operating temperature | 0 - 45 °C |
|-----------------------|-----------|

**Voltage**

|                            |            |
|----------------------------|------------|
| Input voltage              | 24 - 230 V |
| Operating voltage over bus | 21 - 32 V  |
| Type voltage supply        | AC/DC      |

**Dimensions**

|        |       |
|--------|-------|
| Length | 70 mm |
| Height | 90 mm |
| Depth  | 60 mm |

**Texts**

|                    |                                     |
|--------------------|-------------------------------------|
| Type of connection | With quickconnect plug-in terminals |
|--------------------|-------------------------------------|

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|