



TXA306



**Binary input 6 fold, universal, modular, KNX**

**Technical Features**

**Architecture**

Bus system	EIB
------------	-----

**Settings**

Supported configuration mode	ETS easy
------------------------------	-------------

**Electric current**

Number of entry circuits	6
--------------------------	---

**Equipment**

External signal voltage necessary	No
-----------------------------------	----

**Connectivity**

With bus system KNX radio	No
---------------------------	----

**Equipment**

Radio frequency bidirectional	No
With battery	No
With HVAC control	No

**Installation, mounting**

Mounting on	DIN rail
-------------	----------

**Lighting**

LED controlling	No
-----------------	----

**Materials**

Material	Plastic
Colour	Light grey
RAL code	7035

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	0 - 45 °C
-----------------------	-----------

**Voltage**

Input voltage	24 - 230 V
Operating voltage over bus	21 - 32 V
Type voltage supply	AC/DC

**Dimensions**

Length	70 mm
Height	90 mm
Depth	60 mm

**Texts**

Type of connection	With quickconnect plug-in terminals
--------------------	-------------------------------------

**Sustainability**

RoHS conform	Yes
--------------	-----