



TU402



2-channel remote control

Technical Features

Frequency

| | |
|------------------------------|---------------|
| Frequency transmission | 868 - 868 MHz |
| Radio transmission frequency | 868.30 MHz |

Voltage

| | |
|-------------------|---------|
| Operating voltage | 6 - 6 V |
|-------------------|---------|

Functions

| | |
|--|-------|
| Max. radio transmission range outdoors | 100 m |
|--|-------|

Connectivity

| | |
|-------------------|-----------|
| Radio protocol | KNX Radio |
| Receiver category | 2 |

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 2 |
|-------------------|---|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP50 |
|-------------------------------|------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10 - 45 °C |
|-----------------------|-------------|

Dimensions

| | |
|--------|----------|
| Height | 83 mm |
| Width | 46.5 mm |
| Depth | 15.80 mm |

Equipment

| | |
|--------------|-----|
| With battery | Yes |
|--------------|-----|

Battery

| | |
|--------------|---------|
| Battery life | 5 years |
|--------------|---------|

Texts

| | |
|----------|--|
| Function | Easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control Reset function (to factory setting) |
|----------|--|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|