



TYF784



Analog input device 4-gang KNX

Technical Features

Voltage

Operating voltage over bus	21 - 32 V
----------------------------	-----------

Settings

Supported configuration mode	ETS
------------------------------	-----

Voltage

Auxiliary tension	24 - 24 V
-------------------	-----------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Current consumption	170 mA
---------------------	--------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Capacity

Number of modules	4
-------------------	---

Sustainability

Halogen free	Yes
--------------	-----

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----