




TYF784



Analog input device 4-gang KNX

Technical Features

Voltage

Operating voltage over bus 21 - 32 V

Settings

Supported configuration mode ETS

Voltage

Auxiliary tension 24 - 24 V

Frequency

Frequency 50 - 60 Hz

Power

Current consumption 170 mA

Use conditions

Operating temperature -5 - 45 °C

Capacity

Number of modules 4

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes