



TX211A



**Dimmer 3 outputs KNX, 1/10V**

**Technical Features**

**Voltage**

Operating voltage over bus	21 - 32 V
System supply voltage	30 V DC Via bus

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Use conditions**

Operating temperature	0 - 45 °C
-----------------------	-----------

**Connection**

Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>

**Equipment**

Number of outputs	3
Type of dimmer	1 - 10 V

**Capacity**

Number of modules	4
-------------------	---

**Power**

230 V incandescent and halogen lamp	2300 W
Power of variator	0 - 2300 W

**Connectivity**

With bus system KNX radio	No
Type of connection	Screw terminal

**Settings**

Supported configuration mode	ETS
------------------------------	-----

**Texts**

Type of connection	With screw terminals
--------------------	----------------------

**Sustainability**

RoHS conform	Yes
--------------	-----