




EV106



## Remote control dimmer 1-10V

### Technical Features

#### Voltage

Operating voltage 230 - 230 V

#### Frequency

Frequency 50 - 50 Hz

#### Connectivity

Dimming DALI No

#### Power

Power consumption during operation 3 VA

Power consumption standby 1 W

#### Use conditions

Operating temperature -10 - 45 °C

#### Dimensions

Height 85 mm

Width 71 mm

Depth 65 mm

#### Connection

Cross-section rigid conductor 1.5 - 10 mm<sup>2</sup>

Cross-section flexible conductor 1 - 6 mm<sup>2</sup>

#### Capacity

Number of modules 4

#### Electric current

Control current 1-10 V slave 50 mA

#### Materials

Colour Grey

#### Texts

Type of connection With screw terminals

Installation mode For mounting on DIN rail

Junction Connection for illuminated (max. 5 mA) or standard push-buttons

#### Sustainability

RoHS conform Yes