




EV106



Remote control dimmer 1-10V

Technical Features

Voltage

Operating voltage 230 - 230 V

Frequency

Frequency 50 - 50 Hz

Connectivity

Dimming DALI No

Power

Power consumption during operation 3 VA

Power consumption standby 1 W

Use conditions

Operating temperature -10 - 45 °C

Dimensions

Height 85 mm

Width 71 mm

Depth 65 mm

Connection

Cross-section rigid conductor 1.5 - 10 mm²

Cross-section flexible conductor 1 - 6 mm²

Capacity

Number of modules 4

Electric current

Control current 1-10 V slave 50 mA

Materials

Colour Grey

Texts

Type of connection With screw terminals

Installation mode For mounting on DIN rail

Junction Connection for illuminated (max. 5 mA) or standard push-buttons

Sustainability

RoHS conform Yes