



TXB692F



Output module 2x 6A /230V~, 2 inputs, flush mounted, KNX

Technical Features

Settings

Supported configuration mode	ETS easy
------------------------------	-------------

Connectivity

With bus system KNX radio	No
---------------------------	----

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Materials

Colour	Light grey
--------	------------

Equipment

With switch for manual switch	Yes
-------------------------------	-----

Electric current

Rated current	6 A
Max. switching current	6 A

Voltage

Operating voltage over bus	21 - 32 V
----------------------------	-----------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Connection

Cross-section flexible conductor	0.75 - 2.5 mm ²
Cross-section rigid conductor	0.75 - 2.5 mm ²

Capacity

Number of modules	0
-------------------	---

Texts

Function	With safety functions e.g. for wind, rain, alarm Binary input functions: Switching, dimming, blind, value transmitter, scene, priority, timer operation, subplate With positioning function for blind and lamella position
Type of connection	With screw terminals

Sustainability

RoHS conform	Yes
--------------	-----