



TRE302



**RF external double push button wall mounted**

**Technical Features**

**Installation, mounting**

Mounting on Surface mounting

**Use conditions**

Operating temperature -10 - 55 °C

**Frequency**

Radio transmission frequency 868.30 MHz

**Connectivity**

Receiver category 2

Radio protocol KNX Radio

**Functions**

With room temperature controller No

**Voltage**

Operating voltage 3 - 3 V

**Dimensions**

Built-in depth flush-mounted boxes 25 mm

Height 76 mm

Width 49 mm

**Materials**

Colour White

RAL code 9010

Material Plastic

Surface finish Glossy  
Matt

**Accessories**

Has labelling field No

**Texts**

Function Easy additional functions: +6 scenes, on/off operating mode, 1 up/  
down button control  
Configuration can simply be transferred from a master device  
Reset function (to factory setting)

Installation mode For screw fastening or For mounting with adhesive mounting  
For vertical and horizontal mounting

**Sustainability**

RoHS conform Yes