



TRE302



RF external double push button wall mounted

Technical Features

Installation, mounting

Mounting on Surface mounting

Use conditions

Operating temperature -10 - 55 °C

Frequency

Radio transmission frequency 868.30 MHz

Connectivity

Receiver category 2

Radio protocol KNX Radio

Functions

With room temperature controller No

Voltage

Operating voltage 3 - 3 V

Dimensions

Built-in depth flush-mounted boxes 25 mm

Height 76 mm

Width 49 mm

Materials

Colour White

RAL code 9010

Material Plastic

Surface finish Glossy
Matt

Accessories

Has labelling field No

Texts

Function Easy additional functions: +6 scenes, on/off operating mode, 1 up/
down button control
Configuration can simply be transferred from a master device
Reset function (to factory setting)

Installation mode For screw fastening or For mounting with adhesive mounting
For vertical and horizontal mounting

Sustainability

RoHS conform Yes