



TXA304



Binary input 4 fold, 230V~, modular, KNX

### Technical Features

#### Architecture

|            |     |
|------------|-----|
| Bus system | EIB |
|------------|-----|

#### Settings

|                              |             |
|------------------------------|-------------|
| Supported configuration mode | ETS<br>easy |
|------------------------------|-------------|

#### Electric current

|                          |   |
|--------------------------|---|
| Number of entry circuits | 4 |
|--------------------------|---|

#### Equipment

|                                   |    |
|-----------------------------------|----|
| External signal voltage necessary | No |
|-----------------------------------|----|

#### Connectivity

|                           |    |
|---------------------------|----|
| With bus system KNX radio | No |
|---------------------------|----|

#### Equipment

|                               |    |
|-------------------------------|----|
| Radio frequency bidirectional | No |
| With battery                  | No |
| With HVAC control             | No |

#### Installation, mounting

|             |          |
|-------------|----------|
| Mounting on | DIN rail |
|-------------|----------|

#### Lighting

|                 |    |
|-----------------|----|
| LED controlling | No |
|-----------------|----|

#### Materials

|          |            |
|----------|------------|
| Material | Plastic    |
| Colour   | Light grey |
| RAL code | 7035       |

#### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

#### Use conditions

|                       |           |
|-----------------------|-----------|
| Operating temperature | 0 - 45 °C |
|-----------------------|-----------|

#### Voltage

|                            |             |
|----------------------------|-------------|
| Input voltage              | 230 - 230 V |
| Operating voltage over bus | 21 - 32 V   |
| Type voltage supply        | AC          |

#### Dimensions

|        |       |
|--------|-------|
| Length | 35 mm |
| Height | 90 mm |
| Depth  | 69 mm |

#### Texts

|                    |                                     |
|--------------------|-------------------------------------|
| Type of connection | With quickconnect plug-in terminals |
|--------------------|-------------------------------------|

#### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|