



TXA304



Binary input 4 fold, 230V~, modular, KNX

Technical Features

Architecture

Bus system	EIB
------------	-----

Settings

Supported configuration mode	ETS easy
------------------------------	-------------

Electric current

Number of entry circuits	4
--------------------------	---

Equipment

External signal voltage necessary	No
-----------------------------------	----

Connectivity

With bus system KNX radio	No
---------------------------	----

Equipment

Radio frequency bidirectional	No
With battery	No
With HVAC control	No

Installation, mounting

Mounting on	DIN rail
-------------	----------

Lighting

LED controlling	No
-----------------	----

Materials

Material	Plastic
Colour	Light grey
RAL code	7035

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	0 - 45 °C
-----------------------	-----------

Voltage

Input voltage	230 - 230 V
Operating voltage over bus	21 - 32 V
Type voltage supply	AC

Dimensions

Length	35 mm
Height	90 mm
Depth	69 mm

Texts

Type of connection	With quickconnect plug-in terminals
--------------------	-------------------------------------

Sustainability

RoHS conform	Yes
--------------	-----