



TKC110



Power supply with adapters for Coviva smartbox TKP100A

Technical Features

Electric current

Output current	3000 mA
Intensity output 1	3 A

Functions

Output voltage adjusted	Yes
-------------------------	-----

Frequency

Frequency	50 - 50 Hz
-----------	------------

Capacity

Number of modules	0
-------------------	---

Voltage

Output voltage	5 - 5 V
----------------	---------

Use conditions

Operating temperature	0 - 45 °C
-----------------------	-----------

Connectivity

Type of connection	Plug-in connection
--------------------	--------------------

Dimensions

Height	33.25 mm
--------	----------

Sustainability

RoHS conform	Yes
--------------	-----