



TRE400



Module 1 input + 1 output, 10A, IP55, KNX radio

Technical Features

Equipment

C load	No
Number of channels	1
Number of outputs	1

Architecture

Number of blinds/shutter outputs	0
----------------------------------	---

Connectivity

With bus system radio frequent	Yes
Receiver category	2
Radio protocol	KNX Radio

Equipment

Transmitter duty cycle	1 %
------------------------	-----

Frequency

Radio reception frequency	868.30 - 868.30 MHz
---------------------------	---------------------

Equipment

With switch for manual switch	Yes
-------------------------------	-----

Dimensions

Height	35 mm
--------	-------

Voltage

Input voltage	5 - 5 V
Operating voltage	230 - 230 V

Dimensions

Length	150 mm
Width	85 mm

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Number of entry circuits	1
Switching current	10 A
Rated current	10 A

Power

Power incandescent lamp	1500 - 1500 W
-------------------------	---------------

Use conditions

Operating temperature	-10 - 55 °C
-----------------------	-------------

Texts

Cable clamp	With mounting plates and strain reliefs
Function	Easy additional functions: +6 scenes Repeat function can be activated to increase the radio range Reset function (to factory setting)
Installation mode	For installation behind flush-mounted inserts
Type of connection	With screw-in lift terminals

Sustainability

RoHS conform	Yes
--------------	-----