



TRE400



Module 1 input + 1 output, 10A, IP55, KNX radio

Technical Features

Connectivity

Radio protocol	KNX Radio
----------------	-----------

Settings

Supported configuration mode	ETS easy
------------------------------	-------------

Connectivity

Receiver category	2
With bus system KNX	No
With bus system KNX radio	Yes

Dimensions

Dimensions	35 x 85 mm
Height	35 mm
Width	85 mm
Depth	53 mm

Electric current

Rated current IN	10 A
------------------	------

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Architecture

Bus system	KNX
------------	-----

Materials

Colour	White
--------	-------

Equipment

Radio frequency bidirectional	Yes
With switch for manual switch	Yes

Electric current

Switching current	10 A
-------------------	------

Frequency

Frequency	50 - 50 Hz
Radio reception frequency	868.30 - 868.30 MHz

Power

Output power	2300 W
230 V incandescent and halogen lamp	1500 W
Power incandescent lamp	1500 - 1500 W

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Safety

Ingress Protection (IP) class	IP55
-------------------------------	------

Use conditions

Operating temperature	-10 - 55 °C
-----------------------	-------------

Texts

Function	Easy additional functions: +6 scenes Repeat function can be activated to increase the radio range Reset function (to factory setting)
Installation mode	For installation behind flush-mounted inserts
Type of connection	With screw-in lift terminals

Sustainability

RoHS conform

Yes