



TRB201



Module 1 output 16A flush mounted KNX

Technical Features

Connectivity

Radio protocol	KNX Radio
----------------	-----------

Settings

Supported configuration mode	ETS easy
------------------------------	-------------

Connectivity

Receiver category	2
With bus system KNX	No
With bus system KNX radio	Yes

Dimensions

Height	30 mm
Built-in depth	35 mm

Electric current

Rated current	16 A
---------------	------

Materials

Colour	Light grey
--------	------------

Equipment

Radio frequency bidirectional	Yes
With switch for manual switch	No

Electric current

Switching current	16 A
-------------------	------

Frequency

Frequency	50 - 60 Hz
Radio reception frequency	868.30 - 868.30 MHz

Power

Output power	3680 W
230 V incandescent and halogen lamp	2300 W

Voltage

Operating voltage	230 - 230 V
Rated operational voltage U _e	230 - 230 V
System supply voltage	230 V AC

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	0 - 45 °C
-----------------------	-----------

Connection

Cross-section rigid conductor	2.5 mm ²
Cross-section flexible conductor	2.5 mm ²

Texts

Function	Easy additional functions: +6 scenes, repeater function Reset function (to factory setting)
Installation mode	For installation behind flush-mounted inserts
Type of connection	With screw-in lift terminals

Sustainability

RoHS conform	Yes
--------------	-----