



EK054



IP30



Room thermostat with

Technical Features

Electric current

Switching current 10 A

Power supply

Supply voltage 230 V +10%/-15%

Frequency

Frequency 50 - 60 Hz

Settings

Comfort temperature setpoint 5 - 35 °C

Materials

Colour White

RAL code 9010

Surface finish Matt

Dimensions

Height 82 mm

Width 82 mm

Screen

With display No

Equipment

Switching temperature difference 0.50 K

Type of thermostat Room thermostat

Type of probe Room sensor

Safety

Ingress Protection (IP) class IP30

Connection

Type of contacts 1NO

Use conditions

Energy efficiency class I (1%)

Texts

Installation mode Suitable for surface mounting or for mounting on flush-mounted boxes

Type of connection With screw terminals

Thermal re-circulation With thermal return

Sustainability

RoHS conform Yes