



EK054



IP30



**Room thermostat with**

**Technical Features**

**Electric current**

Switching current	10 A
-------------------	------

**Power supply**

Supply voltage	230 V +10%/-15%
----------------	-----------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Settings**

Comfort temperature setpoint	5 - 35 °C
------------------------------	-----------

**Materials**

Colour	White
RAL code	9010
Surface finish	Matt

**Dimensions**

Height	82 mm
Width	82 mm

**Screen**

With display	No
--------------	----

**Equipment**

Switching temperature difference	0.50 K
Type of thermostat	Room thermostat
Type of probe	Room sensor

**Safety**

Ingress Protection (IP) class	IP30
-------------------------------	------

**Connection**

Type of contacts	1NO
------------------	-----

**Use conditions**

Energy efficiency class	I (1%)
-------------------------	--------

**Texts**

Installation mode	Suitable for surface mounting or for mounting on flush-mounted boxes
Type of connection	With screw terminals
Thermal re-circulation	With thermal return

**Sustainability**

RoHS conform	Yes
--------------	-----