



EGK103

### Digital time switch 1 Channel weekly cycle + Bluetooth key

#### Technical Features

##### Voltage

Nominal voltage	230 - 230 V
Rated operational voltage U <sub>e</sub>	230 - 230 V

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Power

230 V incandescent and halogen lamp	2300 W
-------------------------------------	--------

##### Lighting

Max. load fluorescent lamp in series	1000 W
Max. load fluorescent lamp parallel compensated	400 VA

##### Functions

Power reserve in years	5 y
With network synchronisation	No
With quartz synchronisation	Yes
Number of function channels	1

##### Equipment

Accuracy per day	1.50 s
With impulse programme	No
Number of channels	1

##### Connection

Type of contacts	1x changeover
------------------	---------------

##### Settings

Daily programme	Yes
Weekly programme	Yes
Annual programme	No

##### Use conditions

Operating temperature	-5 - +45 °C
-----------------------	-------------

##### Connection

Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>

##### Texts

Type of connection	With screw terminal
--------------------	---------------------

##### Dimensions

Height	85 mm
Width	35.80 mm
Depth	61.60 mm

##### Main electrical attributes

Minimum interval between 2 switching times	1 min
--	-------

##### Capacity

Number of modules	2
-------------------	---

##### Sustainability

RoHS conform	Yes
--------------	-----