



85121100



Universal - Switch Insert 1gang

Technical Features

Voltage

Operating voltage 230 - 230 V

Controls and indicators

Applicable with movement sensor Yes

Lighting

LED lamp power 250 W

Frequency

Frequency 50 - 60 Hz

Functions

leading edge dimmer Yes

trailing edge dimmer Yes

Lighting

Dimmable 230 V LED lamp 3 - 250 W

Power

Power consumption standby 0.30 W

Capacity

Number of modules 0

Use conditions

Operating temperature -5 - 45 °C

Dimensions

Built-in depth 32 mm

Texts

Dimming principle Automatic setting of load-dependent switching principle (autodetect process)

Extension unit input With extension unit input for push-button (NO contact), single-surface operation and motion detector extension unit

Fuse Short-circuit and overload-proof (electronic fuse)

Installation mode With spreader claws

Type of connection With screw terminals

Sustainability

RoHS conform Yes