



TRM600



### Control for latching relay, timer KNX radio

#### Technical Features

##### Connectivity

Radio protocol	KNX Radio
----------------	-----------

##### Settings

Supported configuration mode	ETS easy
------------------------------	-------------

##### Connectivity

Receiver category	2
With bus system KNX	No
With bus system KNX radio	Yes

##### Dimensions

Dimensions	18 x 40 mm
Height	18 mm
Width	40 mm
Depth	18 mm
Built-in depth	20 mm

##### Electric current

Rated current	0.50 A
---------------	--------

##### Materials

Colour	Light grey
--------	------------

##### Equipment

Radio frequency bidirectional	Yes
With switch for manual switch	Yes

##### Frequency

Frequency	50 - 60 Hz
Radio reception frequency	868.30 - 868.30 MHz

##### Power

Output power	115 W
--------------	-------

##### Voltage

Operating voltage	230 - 230 V
Rated operational voltage Ue	230 - 230 V
System supply voltage	230 V AC

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Use conditions

Operating temperature	-15 - 45 °C
-----------------------	-------------

##### Connection

Cross-section rigid conductor	0.5 - 2.5 mm <sup>2</sup>
Cross-section flexible conductor	0.5 - 1.5 mm <sup>2</sup>

##### Texts

Function	Pulse function only Reset function (to factory setting)
Installation mode	For installation behind flush-mounted inserts
Type of connection	With screw-in lift terminals

##### Sustainability

RoHS conform	Yes
--------------	-----