



WNA105B

### cubyko Socket 2P+E detrompage composable white IP55

#### Technical Features

##### Electric current

Rated current	16 A
---------------	------

##### Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

##### Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Colour	Pure white
RAL code	9010
Surface finish	Matt
Material	Polycarbonate (PC) Polypropylene (PP)
Treatment	Untreated

##### Dimensions

Height	75 mm
Width	75 mm
Depth	22.80 mm
Number of units	1
Built-in depth flush-mounted boxes	35 mm

##### Connection

Connector/plug type	Turn screw lock
---------------------	-----------------

##### Installation, mounting

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

##### Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting

##### Equipment

Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	Yes
With signal lamp	No
With lock	No

##### Accessories

Has labelling field	Yes
---------------------	-----

##### Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

##### Capacity

Number of modules	2
-------------------	---

##### Safety

With enhanced contact protection	Yes
Impact resistance IK	IK07
Ingress Protection (IP) class	IP55

<b>Functions</b>		
With orientation lighting		No
With function lighting		No
<b>Identification</b>		
With imprint		No
<b>Texts</b>		
Imprint		With imprint
Cover	For covering of socket outlets	
Protection	Without protective screen	
<b>Suitable for</b>		
Hager cubyko		
<b>Sustainability</b>		
REACH-SVHC free		Yes
RoHS conform		Yes