



WNA105B



IP55

cubyko Socket 2P+E detrompage composable white IP55

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Use conditions

Operating temperature -15 - 30 °C

Frequency

Frequency 50 - 60 Hz

Materials

Colour Pure white
RAL code 9010
Surface finish Matt
Material Polycarbonate (PC)
Polypropylene (PP)
Treatment Untreated

Dimensions

Height 75 mm
Width 75 mm
Depth 22.80 mm
Number of units 1
Built-in depth flush-mounted boxes 35 mm
Height of P-touch band for labelling field 12 mm

Connection

Connector/plug type Turn screw lock
Cross-section flexible conductor without wire end sleeve 1.0 - 2.5 mm²

Installation, mounting

Mounting on Flush mounting
Surface mounting
Mounting-/Connection Position Horizontal

Connectivity

Type of connection Plug-in connection
Mounting type Screw mounting

Equipment

Connector/plug type socket outlet Earthing pin
Rotated central insert No
With hinged lid Yes
With round protective earth pin Yes
With signal lamp No
With lock No

Accessories

Has labelling field Yes
Pre-equipped with Socket outlet

Cover, door

Type of lid Self-closing hinged cover, can be arrested in end position

Capacity

Number of modules 2

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK07
Ingress Protection (IP) class	IP55
Usable in higher IP class	IP55 with closed cover

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Cover	For covering of socket outlets
Protection	Without protective screen
Type of connection	With plug-in terminals
Labelling	Without labelling

Suitable for

cubyko	
--------	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes