



WXF070

Connected dimmer gallery

Technical Features

Voltage

Operating voltage 230 - 230 V

Frequency

Frequency 50 - 50 Hz

Materials

Colour White

RAL code 7011

Material Polycarbonate (PC)

Dimensions

Height 45 mm

Width 45 mm

Depth 37 mm

Architecture

Control/operation element Single push button

Power

Power incandescent lamp 20 - 275 W

Use conditions

Operating temperature -10 - 35 °C

Capacity

Number of modules 2

Texts

Dimming principle Phase cut-on or cut-off according to load type, self-learning

Installation mode For catch fixing

Type of connection With screw terminals

Operation and control App control via Bluetooth

Equipment

Substation input Yes

Sustainability

RoHS conform Yes