



6768776084

**Earthing pin socket outlet w hinged cover + plug-in terminal Q.x alu velvety**

**Technical Features**

**Voltage**

Rated voltage	250 V
---------------	-------

**Electric current**

Rated current	16 A
---------------	------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Aluminium
RAL code	9006
Surface finish	Velvety
Material	Thermoplastic
Treatment	Varnished

**Dimensions**

Width	71 mm
Number of units	1
Built-in depth flush-mounted boxes	35 mm
Built-in depth	31.20 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Mounting type	Claw mounting Screw mounting
---------------	---------------------------------

**Equipment**

Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	Yes
With signal lamp	No

**Accessories**

Has labelling field	No
---------------------	----

**Cover, door**

Type of lid	Self-closing hinged cover
-------------	---------------------------

**Capacity**

Number of modules	1
-------------------	---

**Safety**

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

**Functions**

With orientation lighting	No
With function lighting	No

**Identification**

With imprint	No
--------------	----

**Texts**

Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With plug-in terminals

---

**Suitable for**

Q.x

---

**Sustainability**

---

REACH-SVHC free

Yes

---

RoHS conform

Yes

---