



6719333502

Surface-mtd housing 2gang vert., frame surface-mtd, W.1, p.white, matt, plastic

Technical Features

Capacity

Number of modules	2
-------------------	---

Materials

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	147 mm
Width	76 mm
Depth	56 mm

Equipment

With cable entry	Yes
------------------	-----

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Accessories

With frame cover	Yes
------------------	-----

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Installation mode	For vertical mounting
Sealing	With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes