



SPN015D

Cartridge 15kA 275V for pluggable SPD

Technical Features

Capacity

Number of modules	1
-------------------	---

Voltage

Rated operational voltage U_e	230 - 230 V
Continuous operating voltage U_c according to IEC 61643-1	275 V
Voltage protection level U_p according to IEC 61643-1	1 kV

Electric current

Nominal discharge current I_n 8 - 20 μ s L-N(PEN)/N-PE IEC 61643	5 kA
Max. discharge (I_{max}) L-N(PEN)/ N-PE	15 kA

Dimensions

Height	45 mm
Width	18 mm
Depth	18 mm

Use conditions

Operating temperature	-40 - 55 °C
-----------------------	-------------

Network configuration

Network type	TN-C TN-S TT
--------------	--------------------

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes