



EZL100



**Emergency light tester time relay 230V AC**

**Technical Features**

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Use conditions**

Operating temperature	-25 - 55 °C
Storage/transport temperature	-25 - 70 °C

**Connection**

Cross-section flexible conductor	0.5 - 2.5 mm <sup>2</sup>
Cross-section rigid conductor	0.5 - 2.5 mm <sup>2</sup>
Number of contacts	1
Type of contacts	1x changeover

**Capacity**

Number of modules	1
-------------------	---

**Dimensions**

Height	87 mm
Width	17.50 mm
Depth	65 mm

**Electric current**

Acceptable current rating AC1	8 A
-------------------------------	-----

**Equipment**

Number of NC contacts	0
Number of NO contacts	1
Switch off delay	No
Switch on delay	No

**Settings**

Time delay	10 Min - 180 Min
------------	------------------

**Voltage**

Command voltage for 50 Hz	230 - 230 V
Command voltage for 60 Hz	230 - 230 V
Type voltage supply	AC

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes