



SPN008D

Cartridge 8kA 255V for pluggable SPD

Technical Features

Capacity

Number of modules

1

Voltage

Rated operational voltage Ue

230 - 230 V

Continuous operating voltage Uc according to IEC 61643-1

275 V

Voltage protection level Up according to IEC 61643-1

1 kV

Electric current

Nominal discharge current In 8 - 20 μ s L-N(PEN)/N-PE IEC 61643

15 kA

Max. discharge (Imax) L-N(PEN)/ N-PE

40 kA

Dimensions

Height

45 mm

Width

17.5 mm

Depth

43 mm

Use conditions

Operating temperature

-40 - 55 °C

Network configuration

Network type

TN

TT

Standards

Requirement class IEC 61643

T2

Frequency

Frequency

50 - 60 Hz