



SPN008D

Cartridge 8kA 255V for pluggable SPD

Technical Features

Capacity

Number of modules	1
-------------------	---

Voltage

Rated operational voltage U_e	230 - 230 V
Continuous operating voltage U_c according to IEC 61643-1	275 V
Voltage protection level U_p according to IEC 61643-1	1 kV

Electric current

Nominal discharge current I_n 8 - 20 μ s L-N(PEN)/N-PE IEC 61643	15 kA
Max. discharge (I_{max}) L-N(PEN)/ N-PE	40 kA

Dimensions

Height	45 mm
Width	17.5 mm
Depth	43 mm

Use conditions

Operating temperature	-40 - 55 °C
-----------------------	-------------

Network configuration

Network type	TN TT
--------------	----------

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------